

Rittal – The System.

Faster – better – everywhere.



SV 9340.860 Cable set

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.860 - Cable set for OM adapter with spring-cage terminal

Pre-assembled connection cables for the individual connection of switchgear.



Features

Model No.	SV 9340.860
Product description	Pre-assembled connection cables for individual connection of switchgear, top-mounted on OM adaptors with tension spring clamps.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
Note	AWG = American Wire Gage
AWG	AWG 12 = 3.31 mm ² ∅ 4 mm ²
Dimensions	Length: 140 mm Length: 5.51 "
Packaging unit	15 pc(s).
Net weight	0.075 kg
Gross weight	0.085 kg
Copper weight (kg per piece)	0.003
Customs tariff number	85444290
ETIM 9	EC000839
ECLASS 8.0	27062302

Features

Product description

SV Cable set, AWG 12, L: 140 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK