

Rittal – The System.

Faster – better – everywhere.



VX 8660.024

Base/plinth corner pieces with base/plinth trim panels, front and rear

State: 4/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.024 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, carbon steel

Base/plinth corner pieces with trim panels for flexible cable entry.



Features

Model No.	VX 8660.024
Benefits	Reliable - very high stability of the base Flexible – numerous interior expansion options with the VX accessories Simple – flush finish between the baying points
Material	Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner and baying covers: Plastic
Color	RAL 9005
Supply includes	4 x corner covers Assembly components 4 x base/plinth corner pieces, 200 mm high 1 base/plinth trim panel, front/rear, 200 mm 2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths

Features

Dimensions	Height: 200 mm Height: 7.87 "
Suitable for	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 1,000 mm Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 39.4 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	10.2 kg 22.5 lb.
Packaging unit	2 pc(s).
Net weight	10.232 kg
Gross weight	10.239 kg
PCF/VE (cradle-to-gate)	38.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
ETIM 9	EC000721

Features

ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base corner piece with base trim panel, front and rear, : 200 mm, for W H: 1000 mm, carbon steel

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration
