

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.870 Cable set

State: 6/17/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.870 - Cable set for OM adapter with spring-cage terminal

Pre-assembled connection cables for the individual connection of switchgear.



## Features

Model No.	SV 9340.870
Product description	Pre-assembled connection cables for individual connection of switchgear, top-mounted on OM adaptors with tension spring clamps.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
Note	AWG = American Wire Gage
AWG	AWG 10 = 5.26 mm <sup>2</sup> $\times$ 6 mm <sup>2</sup>
Dimensions	Length: 140 mm Length: 5.51 "
Packaging unit	15 pc(s).
Net weight	0.12 kg
Gross weight	0.13 kg
Copper weight (kg per piece)	0.006
Customs tariff number	85444290
ETIM 9	EC000839
ECLASS 8.0	27062302

# Features

---

Product description

SV Cable set, AWG 10, L: 140 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK