

Rittal – The System.

Faster – better – everywhere.



SV 9340.880 Cable set

State: 7/11/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.880 - Cable set for OM adapter with spring-cage terminal

Pre-assembled connection cables for the individual connection of switchgear.



Features

Model No.	SV 9340.880
Product description	Pre-assembled connection cables for individual connection of switchgear, top-mounted on OM adaptors with tension spring clamps.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 8 = 8.37 mm ² ÷ 10 mm ²
Note	AWG = American Wire Gage
Dimensions	Length: 140 mm Length: 5.51 "
Packaging unit	6 pc(s).
Net weight	0.06
Gross weight	0.088
Copper weight (kg per piece)	0.009
Customs tariff number	85444290
EAN	4028177502734
ETIM 9	EC000839

Features

ECLASS 8.0	27062302
------------	----------

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---