Rittal – The System.

Faster – better – everywhere.





SV 9340.950 Bus-mounting fuse base D-Switch

State: 11/3/2025 (Source: rittal.com/us-en)



SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

Features

Model No.	SV 9340.950
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035 Fuse holder: RAL 7001
Supply includes	Incl. reducing retaining springs for D 01 and 10 x 38 mm fuses
Note	Wire end ferrules should be used with fine stranded wire conductors
For bar systems with center-to- center spacing	60 mm
Type of connection (electrical)	Box terminal
Fuse inserts	D 01 (with reducer) D 02 (with Neozed adaptor sleeve) 10 x 38 (with retaining spring)
Fuse inserts footnote	When using D 01 and 10 x 38 mm fuses, it is necessary to use reducers. Optional use of D 01 fuses with adaptor sleeve for D 02 base/plinth possible.
Rated operating current max.	63 A
Rated operating voltage	400 V, 3~
Note	For the use of fuse inserts to DIN EN 60 269-3 (DIN VDE 0636-3) With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors up to 6 mm ²
Test specification	IEC 60 947-3
Dimensions	Width: 27 mm Height: 226 mm Width: 1.06 " Height: 8.9 "

© Rittal 2025

Features

Connection of round conductors	1.5 - 25 mm²
Suitable for busbars	Height: 5, 10 mm
	Height: 0.2, 0.39 "
Voltage range for indicator lights	100 - 400 V
Number of poles	3-pole
Packaging unit	3 pc(s).
Net weight	0.975
Gross weight	1.04
Copper weight (kg per piece)	0.066
Customs tariff number	85369095
EAN	4028177603400
ETIM 9	EC001046
ECLASS 8.0	27371402

Approvals

Explanations	Declaration of conformity
-//	- co.a.a

© Rittal 2025 3