


Rittal – The System.

Faster – better – everywhere.



VX 8660.053

Base/plinth corner piece with base/
plinth trim panel, front and rear for
VX base/plinth system, stainless
steel



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

VX 8660.053 - Base/plinth corner piece with base/plinth trim panel, front and rear for VX base/plinth system, stainless steel new version/design

Base/plinth corner pieces with front and rear panel. Large openings in the base/plinth corner piece for best access to the screw-fastening point. Seamless baying.



Features

Model No.	VX 8660.053
Material	Base/plinth corner piece: Stainless steel 1.4301 (AISI 304) Base/plinth trim panels, front/rear: Stainless steel 1.4301 (AISI 304) Cover caps: ABS
Surface finish	Brushed, grain 400
Supply includes	Assembly components 4 x base/plinth corner pieces 4 cover caps 2 x base/plinth trim panels, front/rear, 100 mm high
Note	Base/plinth side trim panels are required to finish a base/plinth unit and together provide additional stabilization of the base/plinth. The cover caps included in the delivery scope can be replaced with stainless steel cover caps for the VX base/plinth system. The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system
Dimensions	Height: 100 mm Height: 3.94 "

Features

Suitable for	Enclosure type: VX VX SE TS PC Width: = 1,200 mm Enclosure type: VX VX SE TS PC Width: = 47.2 "
--------------	--

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
---------------------------------	---

Packaging unit	2 pc(s).
----------------	----------

Net weight	6.4
------------	-----

Gross weight	6.5
--------------	-----

Customs tariff number	94039910
-----------------------	----------

EAN	4028177037892
-----	---------------

ETIM 9	EC000721
--------	----------

ETIM 8	EC000721
--------	----------

ECLASS 8.0	27182003
------------	----------

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------