Rittal – The System.

Faster – better – everywhere.



VX 8660.070

Base/plinth panels, on side for VX base/plinth system, stainless steel

State: 11/1/2026 (Source: www.rittal.com/us-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8660.070 - Base/plinth panels, on side for VX base/ plinth system, stainless steel new version/design

Stainless steel base/plinth trim panels are used depth-wise for laterally closing a base/plinth unit.





Features

Model No.	VX 8660.070
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 400
Supply includes	Assembly components
Note	The components of the first generation base/plinth system cannot be combined with the components of the second generation base/ plinth system
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: VX VX SE TS PC Depth: = 400 mm Enclosure type: VX VX SE TS PC Depth: = 15.7 ″

© Rittal 2026

Features

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Packaging unit	2 pc(s).
Net weight	1.31 kg
Gross weight	1.651 kg
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	VX base/plinth trim panel, side, H: 100 mm, for D: 400 mm, stainless steel, 1.4301

Approvals

Approvals	UL + C-UL - FTTA