

Rittal – The System.

Faster – better – everywhere.



VX 8660.090

Base/plinth trim panels, vented

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.090 - Base/plinth trim panels, vented for base/plinth system VX, carbon steel

For enclosure ventilation through the base/plinth. With a 200 mm base/plinth height, one or two vented trim panels may optionally be used. With the optional panel attachment, the ventilated panels can also be mounted on the side of the base corner piece.

Features

Model No.	VX 8660.090
Version	Vented
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 "

Features

Suitable for	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width/depth: 600 mm Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width/depth: 23.6 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	1.42 kg 3.1 lb.
Packaging unit	2 pc(s).
Suitable for	for base/plinth system VX, carbon steel
Net weight	1 kg
Gross weight	1.319 kg
PCF/VE (cradle-to-gate)	17.01
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Features

Product description

VX base trim panel, ventilated, for W/D: 600 mm, sheet steel

Approvals

Explanations

PCF-declaration