


Rittal – The System.

Faster – better – everywhere.



VX 8660.120

Leveling component

State: 2/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.120 - Leveling component for base/plinth system VX, carbon steel

For retrospective leveling on uneven floors at the installation site up to a maximum of 15 mm.
Installed through the base/plinth corner piece.



Features

Model No.	VX 8660.120
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Load capacity	Max. permitted load: 2500 N per leveling component
Note	Can be used in combination with VX, VX IT, VX SE, TX, TS, TS IT, PC, IW or TP with VX socket system Check the load capacity of the floor.
Dimensions	Height: 100 mm Height: 3.94 "
Weight/packaging unit	0.612 kg 1.3 lb.
Packaging unit	4 pc(s).
Suitable for	for base/plinth system VX, carbon steel
Net weight	0.56
Gross weight	0.611
Customs tariff number	73181900
EAN	4028177984813

Features

ETIM 9 EC004043

ETIM 8 EC000721

ECLASS 8.0 27182003