Rittal – The System.

Faster – better – everywhere.





VX 8660.120 Leveling component

State: 12/11/2025 (Source: rittal.com/us-en)



VX 8660.120 - Leveling component for base/plinth system VX, carbon steel

For retrospective leveling on uneven floors at the installation site up to a maximum of 15 mm. Installed through the base/plinth corner piece.



Features

| Model No. | VX 8660.120 | |
|-----------------------|--|--|
| Material | Carbon steel | |
| Surface finish | Zinc-plated | |
| Supply includes | Assembly components | |
| Load capacity | Max. permitted load: 2500 N per leveling component | |
| Note | Can be used in combination with VX, VX IT, VX SE, TX , TS, TS IT, PC, IW or TP with VX socket system Check the load capacity of the floor. | |
| Dimensions | Height: 100 mm Height: 3.94 ″ | |
| Weight/packaging unit | 0.612 kg 1.3 lb. | |
| Packaging unit | 4 pc(s). | |
| Suitable for | for base/plinth system VX, carbon steel | |
| Net weight | 0.56 | |
| Gross weight | 0.611 | |
| Customs tariff number | 73181900 | |
| EAN | 4028177984813 | |
| | | |

© Rittal 2025 2

Features

| ETIM 9 | EC004043 | |
|------------|----------|--|
| ETIM 8 | EC000721 | |
| ECLASS 8.0 | 27182003 | |

© Rittal 2025 3