

# Rittal – The System.

Faster – better – everywhere.



## TS 8800.510 Cable duct

State: 4/25/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8800.510 - Cable duct for vertical TS section

For mounting on a vertical enclosure profile or on two bayed enclosure profiles in the baying area.



## Features

Model No.	TS 8800.510
Version	Width 100 mm, for assembly on two bayed enclosure sections in the baying area.
Benefits	<p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed in combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p>
Material	Hard PVC Flame-resistant, self-extinguishing
Color	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm 0.22 "
Slot width	4.5 mm 0.18 "
Note	Can be shortened for other enclosure sizes.

# Features

---

Dimensions	Width: 100 mm Height: 1,800 mm Depth: 80 mm Width: 3.94 " Height: 70.9 " Depth: 3.15 "
Suitable for	Enclosure type: TS VX SE PC IW Height: ≤ 2,000 mm Enclosure type: TS VX SE PC IW Height: ≤ 78.7 "
Operating temperature range	60 °C 140 °F
Packaging unit	4 pc(s).
Net weight	8.996 kg
Gross weight	9.47 kg
Customs tariff number	39259020
ETIM 9	EC000012
ECLASS 8.0	27400703
Product description	TS Cable duct for vertical TS section, WHD: 100x1800x80 mm

---

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---