
Rittal – The System.

Faster – better – everywhere.





SV 9342.280 Connection Adapters

State: 11/4/2025 (Source: rittal.com/us-en)



SV 9342.280 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

Features

Model No.	SV 9342.280
Material	Cover: ABS
	Punched section: Polyamide
	Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	800 A
Rated operating voltage	690 V, 3~
Cable outlet	Top/bottom
For bar systems with center-to- center spacing	60 mm
Note	The technical data may vary for UL applications.
	UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the
	busbar arrangement in the busbar support
	9340.050/9341.050/9342.050.
	75-10.000/ 75-11.000/ 75-12.000.
Number of poles	3-pole
Dimensions	Width: 129 mm
	Height: 246 mm
	Width: 5.08 "
	Height: 9.69 "
Connection of round conductors, fine wire with wire end ferrule	95 - 185 mm²
Connection of round conductors,	95 - 300 mm²
multi-wire	
multi-wire Suitable for busbars	Height: 5, 10 mm

© Rittal 2025

Features

Clamping area for laminated	33 x 20 mm
copper bars (W x H)	1.3 x 0.79 ["]
Packaging unit	1 pc(s).
Net weight	1.98
Gross weight	2.07
Copper weight (kg per piece)	0.358
Customs tariff number	85369010
EAN	4028177503663
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL
	Lloyds Register of Shipping
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3