
Rittal – The System.

Faster – better – everywhere.



TS 8802.080

Section for cable entry, center


State: 11/3/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8802.080 - Section for cable entry, center for TS, TP

Inserted in base plate.



Features

Model No.	TS 8802.080
Product description	To seal the cable entry between the base plates.
Benefits	Particularly well-suited to cables with identical cross-sections
Technical specifications	Foam rubber cable clamping profile: Cross-section: 30 x 25 mm
Applications	For top-mounting on base plates
Material	Extruded aluminum section Foam rubber cable clamping profile: PU foam
Supply includes	Plug-in sections, incl. foam rubber clamp strip
Note	2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm From an enclosure width of 1,000 mm, two base openings are provided. 4 units per enclosure may be fitted
Suitable for	Enclosure type: TS: = 800 mm Enclosure type: TP Enclosure type: TS: = 31.5 ″ Enclosure type: TP
Protection category IP to IEC 60 529	IP 55 if correctly installed
Packaging unit	2 pc(s).
Net weight	0.3 kg

© Rittal 2026

Features

Gross weight	0.32 kg
Customs tariff number	76042990
ETIM 9	EC000211
ECLASS 8.0	27142421
Product description	TS profile for cable entry, centered, for TS, VX SE, TP, for W: 800 mm