

Rittal – The System.

Faster – better – everywhere.



SV 9342.320 Connection Adapters

State: 8/4/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.320 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

Features

Model No.	SV 9342.320
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	1,600 A
Rated operating voltage	690 V, 3~
Electrical UL ratings (SCCR)	65 kA - 480 V, circuit breaker max. 1200 A, DIVQ/7 65 kA - 600 V, fuse class L max. 1600 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Note	The technical data may vary for UL applications. UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar support 9340.050/9341.050/9342.050.
Number of poles	3-pole
Dimensions	Width: 255 mm Height: 210 mm Width: 10 " Height: 8.27 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Clamping area for laminated copper bars for 5 mm bar thickness, (W x H)	65 x 27 mm 2.56 x 1.06 "

Features

Clamping area for laminated copper bars (W x H)	65 x 22 mm 2.56 x 0.87 "
Clamping area for laminated copper bars for 10 mm bar thickness, (W x H)	65 x 22 mm 2.56 x 0.87 "
Rated operating voltage (L1 + L2)	1000 V (DC)
Rated operating voltage (L1 + L3)	1500 V (DC)
Packaging unit	1 pc(s).
Net weight	2
Gross weight	2.72
Copper weight (kg per piece)	0.408
Customs tariff number	85369010
EAN	4028177525689
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK