

# Rittal – The System.

Faster – better – everywhere.



## TS 8802.125

## Section for cable entry, rear

State: 6/9/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8802.125 - Section for cable entry, rear for TS, TP

Inserted in base opening.

## Features

Model No.	TS 8802.125
Product description	To seal the cable entry on the base opening.
Benefits	Particularly well-suited to cables with identical cross-sections When installing the mounting plate in the rearmost position, the cables may be routed directly without large bending radii.
Technical specifications	Foam rubber cable clamping profile: Cross-section: 30 x 25 mm
Applications	Mount directly on the base opening/base tray and base plate
Material	Extruded aluminum section Foam rubber cable clamping profile: PU foam
Supply includes	Plug-in sections, incl. foam rubber clamp strip
Note	2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm From an enclosure width of 1,000 mm, two base openings are provided. 4 units per enclosure may be fitted
Suitable for	Enclosure type: TS: = 1,200 mm Enclosure type: TP Enclosure type: TS: = 47.2 " Enclosure type: TP
Protection category IP to IEC 60529	IP 55 if correctly installed
Packaging unit	4 pc(s).
Net weight	0.384 kg
Gross weight	0.433 kg
Customs tariff number	76042990
ETIM 9	EC002624
ECLASS 8.0	27189265

# Features

---

Product description

TS profile for cable entry, rear, for TS, VX SE, TP, for W: 1200 mm