Rittal – The System.

Faster – better – everywhere.



# SV 9343.000

# NH Fuse-Switch Disconnectors

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9343.000 - NH Fuse-Switch Disconnectors

## Features

| | |
|---|---|
| Model No. | SV 9343.000 |
| Version | For 60 mm busbar systems |
| Material | Polyamide<br>Fire behavior corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated |
| Color | Chassis: RAL 7035<br>Cover: RAL 7035/7001 |
| Clamping area for laminated copper bars: | Clamping area width: 13 mm<br>Clamping area height: 13 mm<br>Clamping area width: 0.51 ″<br>Clamping area height: 0.51 ″ |
| For bar systems with center-to-center spacing | 60 mm |
| Note | The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses". |
| Cable outlet | Top/bottom |
| Type of connection (electrical) | Box terminal |
| Rated operating current max. | 160 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 00 |
| Test specification | IEC 60 947-3<br>IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 106 mm<br>Height: 194 mm<br>Width: 4.17 ″<br>Height: 7.64 ″ |
| Connection of round conductors | 4 - 95 mm² |

© Rittal 2026

# Features

| | |
|---|---|
| Suitable for busbars | Height: 5, 10 mm<br>Height: 0.2, 0.39 ″ |
| Number of poles | 3-pole |
| Round conductor cross-section | 4 - 95 mm² |
| Packaging unit | 1 pc(s). |
| Net weight | 0.84 kg |
| Gross weight | 0.92 kg |
| Copper weight (kg per piece) | 0.2 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |
| Product description | SV NH fuse-switch disconnector, size 00, 160 A, 690 V, 3-pole, box terminal |

# Approvals

| | |
|---|---|
| Approvals | C-UR<br>CQC-CCC<br>UR + C-UR (recognized) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |