Rittal - The System.

Faster – better – everywhere.





SV 9343.210 NH Fuse-Switch Disconnectors

State: 12/14/2025 (Source: rittal.com/us-en)



SV 9343.210 - NH Fuse-Switch Disconnectors

Features

Model No.	SV 9343.210
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 50 mm Clamping area height: 10 mm Clamping area width: 1.97 " Clamping area height: 0.39 "
For bar systems with center-to- center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	400 A
Rated operating voltage	690 V, 3~
For NH size	2
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm Width: 8.27 " Height: 11.7 "
Connection of round conductors	10 - 240 mm²
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 ″

© Rittal 2025

Features

3-pole
10 - 240 mm²
1 pc(s).
3.358
3.36
1
85369095
4028177540392
EC000249
27371401

Approvals

Approvals	C-UR
	CQC-CCC
	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3