

Rittal – The System.

Faster – better – everywhere.



SV 9344.020

NH Fuse-Switch Disconnectors

State: 11/17/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.020 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

Features

Model No.	SV 9344.020
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 13 mm Clamping area height: 13 mm Clamping area width: 0.51 " Clamping area height: 0.51 "
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	160 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm Width: 4.17 " Height: 7.64 "
Connection of round conductors	4 - 95 mm ²
Number of poles	3-pole
With electronic fuse monitoring	Yes

Features

Cross section round conductor	4 - 95 mm ²
Packaging unit	1 pc(s).
Net weight	0.82
Gross weight	0.837
Copper weight (kg per piece)	0.15
Customs tariff number	85369095
EAN	4028177540521
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK