

Rittal – The System.

Faster – better – everywhere.



SV 9344.130

NH Fuse-Switch Disconnectors

State: 2/12/2026 (Source: ittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.130 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

Features

Model No.	SV 9344.130
Version	For mounting panel assembly. With electronic fuse monitoring
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 32 mm Clamping area height: 10 mm Clamping area width: 1.26 " Clamping area height: 0.39 "
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	250 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	1
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm Width: 7.24 " Height: 11.7 "
Connection of round conductors	10 - 150 mm ²
Number of poles	3-pole

Features

With electronic fuse monitoring	Yes
Round conductor cross-section	10 - 150 mm ²
Packaging unit	1 pc(s).
Net weight	2.3
Gross weight	2.343
Copper weight (kg per piece)	0.3
Customs tariff number	85365080
EAN	4028177540620
ETIM 9	EC000249
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK
