

Rittal – The System.

Faster – better – everywhere.



KEL 9301.000

Ex Enclosures

State: 1/27/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

KEL 9301.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel



Features

Model No.	KEL 9301.000
Version	Ex Enclosures
Applications	<p>Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C...+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)</p>
Material	<p>Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal</p>
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Housing Cover

Features

Dimensions	Width: 150 mm Height: 150 mm Depth: 80 mm Width: 5.91 " Height: 5.91 " Depth: 3.15 "
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Protection category IP to IEC 60 529	IP 66
Packaging unit	1 pc(s).
Net weight	1.2
Gross weight	1.448
Customs tariff number	94032080
EAN	4028177138544
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX ATEX QA CQC-CCC IECEx IECEx QAR
Explanations	Attestation of Conformity