

Rittal – The System.

Faster – better – everywhere.



SV 9344.230

NH Fuse-Switch Disconnectors

State: 5/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.230 - NH Fuse-Switch Disconnectors With electronic fuse monitoring

Features

Model No.	SV 9344.230
Version	For mounting panel assembly.
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 50 mm Clamping area height: 10 mm Clamping area width: 1.97 " Clamping area height: 0.39 "
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	400 A
Rated operating voltage	400 V - 690 V, 3~
For NH size	2
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm Width: 8.27 " Height: 11.7 "
Connection of round conductors	10 - 240 mm ²
Number of poles	3-pole

Features

With electronic fuse monitoring	Yes
Round conductor cross-section	10 - 240 mm ²
Packaging unit	1 pc(s).
Net weight	3.178 kg
Gross weight	3.18 kg
Copper weight (kg per piece)	1
Customs tariff number	85365080
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnecter, size 2, 400 A, 400-690 V, 3-pole, screw M10, with electronic fuse monitoring, for mounting plate assembly

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK