Rittal – The System.

Faster – better – everywhere.



# SV 9345.005
# Fuse Holders

State: 11/10/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9345.005 - Fuse Holders 31 A to 60 A

Fuse holder up to 60 A, 3-pole. Simple mounting on support rails or via OM component adapters.

## Features

| | |
|---|---|
| Model No. | SV 9345.005 |
| Version | For class CC fuse type |
| Material | Polyamide<br>Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Connection for round conductor | AWG 8 - 18 |
| Note | For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adapter combinations (OM adapters/supports) |
| Type of connection (electrical) | Box terminal |
| For fuse type (class) | CC |
| Rated operating current max. | 30 A |
| Rated operating voltage | 600 V, 3~ |
| Fuse standard | UL 248-4 |
| Test specification | UL 4248-1<br>UL 4248-4<br>UL 4248-8 |
| Note on Model No.: | Not suitable for 10 x 38 mm fuses as per IEC 60 269-2/-4/-6 |
| Dimensions | Width: 54 mm<br>Height: 81 mm<br>Width: 2.13 ″<br>Height: 3.19 ″ |
| Connection of round conductors | 0.75 - 25 mm² |

© Rittal 2026

# Features

| | |
|---|---|
| Suitable for fuses | Diameter: 10 mm<br>Length: 38 mm<br>Diameter: 0.39 ″<br>Length: 1.5 ″ |
| Voltage range for indicator lights | 110 - 600 V |
| Electrical UL ratings (SCCR) | 200 kA - 600 V, fuse class CC max. 30 A, JDDZ/7 |
| Number of poles | 3-pole |
| Round conductor cross-section | 0.75 - 25 mm² |
| Packaging unit | 4 pc(s). |
| Net weight | 0.4 kg |
| Gross weight | 0.634 kg |
| Copper weight (kg per piece) | 0.018 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001644 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Fuseholder, Class CC, 30 A, 600 V, 3-pole, (60 mm) |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

© Rittal 2026