

Rittal – The System.

Faster – better – everywhere.



KEL 9305.000 Ex Enclosures

State: 4/29/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9305.000 - Ex Enclosures Stainless steel, empty enclosure with screw fastened cover

Ex Housings with Screw-Fastened Cover, Stainless Steel



Features

| | |
|---------------------------------|---|
| Model No. | KEL 9305.000 |
| Version | Ex Enclosures |
| Applications | Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C...+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb) |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal |
| Surface finish | Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm |
| Supply includes | Housing Cover |
| Dimensions | Width: 400 mm Height: 200 mm Depth: 120 mm Width: 15.7 " Height: 7.87 " Depth: 4.72 " |
| Certificate IEC EX PTB 09.0033U | Yes |

Features

| | |
|-------------------------------------|--|
| Certificate PTB 03 ATEX 1013U | Yes |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Protection category IP to IEC 60529 | IP 66 |
| Packaging unit | 1 pc(s). |
| Net weight | 3.4 kg |
| Gross weight | 3.6 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002503 |
| ECLASS 8.0 | 27180502 |
| Product description | KEL Ex enclosure, WHD: 400x200x120 mm, Stainless steel 1.4301, without mounting plate, Empty enclosure with screw-fastened cover |

Approvals

| | |
|--------------|--|
| Approvals | ATEX ATEX QA CQC-CCC IECEX IECEX QAR |
| Explanations | Attestation of Conformity |