

Rittal – The System.

Faster – better – everywhere.



SV 9345.005 Fuse Holders

State: 6/24/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.005 - Fuse Holders 31 A to 60 A

Fuse holder up to 60 A, 3-pole. Simple mounting on support rails or via OM component adapters.

Features

| | |
|---------------------------------|--|
| Model No. | SV 9345.005 |
| Version | For class CC fuse type |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Connection for round conductor | AWG 8 - 18 |
| Note | For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adapter combinations (OM adapters/supports) |
| Type of connection (electrical) | Box terminal |
| For fuse type (class) | CC |
| Rated operating current max. | 30 A |
| Rated operating voltage | 600 V, 3~ |
| Fuse standard | UL 248-4 |
| Test specification | UL 4248-1 UL 4248-4 UL 4248-8 |
| Note on Model No.: | Not suitable for 10 x 38 mm fuses as per IEC 60 269-2/-4/-6 |
| Dimensions | Width: 54 mm Height: 81 mm Width: 2.13 " Height: 3.19 " |
| Connection of round conductors | 0.75 - 25 mm ² |

Features

| | |
|------------------------------------|---|
| Suitable for fuses | Diameter: 10 mm Length: 38 mm Diameter: 0.39 " Length: 1.5 " |
| Voltage range for indicator lights | 110 - 600 V |
| Electrical UL ratings (SCCR) | 200 kA - 600 V, fuse class CC max. 30 A, JDDZ/7 |
| Number of poles | 3-pole |
| Round conductor cross-section | 0.75 - 25 mm ² |
| Packaging unit | 4 pc(s). |
| Net weight | 0.4 kg |
| Gross weight | 0.634 kg |
| Copper weight (kg per piece) | 0.018 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001644 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Fuseholder, Class CC, 30 A, 600 V, 3-pole, (60 mm) |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |