

# Rittal – The System.

Faster – better – everywhere.



## SV 9345.100 Fuse Holders

State: 6/3/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.100 - Fuse Holders 61 A to 400 A

3-pole, for busbar systems with 60 mm bar center distance.

## Features

Model No.	SV 9345.100
Version	For fuse type class J
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Connection for round conductor	AWG 2 – MCM 300
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
For fuse type (class)	J
Rated operating current max.	100 A
Rated operating current (min.)	61 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Note	UL (listed accessory) is met through use of the fuse holder on RiLine busbar systems
Standards	UL 508
Dimensions	Width: 184 mm Height: 288 mm Width: 7.24 " Height: 11.3 "

# Features

---

Suitable for fuses	Diameter: 29 mm Length: 118 mm Diameter: 1.14 " Length: 4.65 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Electrical UL ratings (SCCR)	100 kA - 600 V, fuse class J max. 100 A, JDDZ/7
Number of poles	3-pole
Packaging unit	1 pc(s).
Net weight	2.61 kg
Gross weight	2.615 kg
Copper weight (kg per piece)	0.837
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuse holder, Class J, 61-100 A, 600 V, 3-pole, (60 mm)

---

# Approvals

---

Approvals	C-UR UL + C-UL (listed) UR + C-UR (recognized)
-----------	--