

Rittal – The System.

Faster – better – everywhere.



SV 9345.704 Circuit-Breaker Component Adaptors

State: 6/16/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.704 - Circuit-Breaker Component Adaptors 4-pole

Features

| | |
|---|--|
| Model No. | SV 9345.704 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Supply includes | Roll of copper Connection screws Contact plates |
| Rated current max. | 500 A |
| Rated operating voltage | 690 V, 4~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications. |
| Cable outlet | Bottom |
| For bar systems with center-to-center spacing | 60 mm |
| Number of poles | 4-pole |
| Dimensions | Width: 185 mm Height: 300 mm Width: 7.28 " Height: 11.8 " |
| Suitable for busbars | Height: 5, 10 mm Height: 0.2, 0.39 " |
| To fit manufacturer (model) | ABB (Tmax T5) |
| Packaging unit | 1 pc(s). |
| Net weight | 3.98 kg |
| Gross weight | 4.027 kg |
| Copper weight (kg per piece) | 2.765 |

Features

| | |
|-----------------------|--|
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 500 A, 690 V, 4-pole, cable outlet bottom, for switchgear make:, ABB |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|