

Rittal – The System.

Faster – better – everywhere.



SV 9345.710 Circuit-Breaker Component Adaptors

State: 6/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.710 - Circuit-Breaker Component Adaptors 3-pole

Circuit breaker adaptor for the universal, simplified assembly of circuit-breakers.



Features

Model No.	SV 9345.710
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Connection straps Sliding Blocks
Rated current max.	630 A
Rated operating voltage	690 V, 3~
Electrical UL ratings (SCCR)	65 kA - 480 V, circuit breaker max. 600 A, DIVQ/7
Cable outlet	Bottom
For bar systems with center-to-center spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications.
Number of poles	3-pole
Note on Model No.:	The 9342.720 insert strip is also required when using Siemens VL630 switchgear

Features

Dimensions	Width: 140 mm Height: 345 mm Width: 5.51 " Height: 13.6 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
To fit manufacturer (model)	ABB (S5, T5, T5 UL) Allen Bradley (140U-L) Eaton (NZM3, NZM3 UL/630 A) GE (FG630) Legrand (DPX 630) Mitsubishi (NF630-SEW/HEW/REW) OEZ (BH630N, BH630S) Schneider Electric (NS(X)630, NSJ600) Schrack (MC3) Siemens (VL630, 3VA24, 3VT3, 3V10 73, 3RV13 73, 3RV13 74, 3VA64) Terasaki (E630, S630)
Approvals	UL
Packaging unit	1 pc(s).
Net weight	3.65 kg
Gross weight	3.8 kg
Copper weight (kg per piece)	2.44
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Circuit-breaker component adaptor, 630 A, 690 V, 3-pole, cable outlet bottom, with connection straps

Approvals

Approvals

Approvals

ABS
DNV
Lloyds Register
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK