

Rittal – The System.

Faster – better – everywhere.



SV 9345.714

Circuit-Breaker Component Adaptors

State: 2/8/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

SV 9345.714 - Circuit-Breaker Component Adaptors 4-pole

Features

Model No.	SV 9345.714
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Roll of copper Connection screws
Rated current max.	500 A
Rated operating voltage	690 V, 4~
Cable outlet	Bottom
For bar systems with center-to-center spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications.
Number of poles	4-pole
Dimensions	Width: 185 mm Height: 300 mm Width: 7.28 " Height: 11.8 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
To fit manufacturer (model)	Schneider Electric
To fit manufacturer (model)	Schneider Electric (NS(X)400, NS(X)630)
Packaging unit	1 pc(s).
Net weight	3.4
Gross weight	3.524
Copper weight (kg per piece)	2.135

Features

Customs tariff number	85369095
EAN	4028177684522
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---
