

Rittal – The System.

Faster – better – everywhere.



SV 9345.730 Circuit-Breaker Component Adaptors

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.730 - Circuit-Breaker Component Adaptors 3-pole

Circuit breaker adaptor for the universal, simplified assembly of circuit-breakers.



Features

| | |
|---|--|
| Model No. | SV 9345.730 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Supply includes | Connection straps Sliding Blocks |
| Rated current max. | 400 A |
| Rated operating voltage | 690 V, 3~ |
| Electrical UL ratings (SCCR) | 65 kA - 480 V, circuit breaker max. 400 A, DIVQ/7 |
| Cable outlet | Bottom |
| For bar systems with center-to-center spacing | 60 mm |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications. |
| Number of poles | 3-pole |
| Dimensions | Width: 140 mm Height: 345 mm Width: 5.51 " Height: 13.6 " |

Features

| | |
|------------------------------|--|
| Suitable for busbars | Height: 5, 10 mm Height: 0.2, 0.39 " |
| To fit manufacturer (model) | Eaton (NZM3, NZM3 UL/400 A) GE (FG400) Mitsubishi (NF400-SEW/HEW/REW) Schneider Electric (NS(X)400, NSJ400) Schrack (MC3) Siemens (VL400, VL400X UL, VL400 UL, 3VA23, 3VA63) Terasaki (E400, S400, H400, L400) |
| Approvals | UL |
| Packaging unit | 1 pc(s). |
| Net weight | 2.831 kg |
| Gross weight | 2.963 kg |
| Copper weight (kg per piece) | 1.533 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 400 A, 690 V, 3-pole, cable outlet bottom, with connection straps |

Approvals

| | |
|--------------|--|
| Approvals | ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |