

Rittal – The System.

Faster – better – everywhere.



SV 9345.734 Circuit-Breaker Component Adaptors

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.734 - Circuit-Breaker Component Adaptors 4-pole

Features

Model No.	SV 9345.734
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Supply includes	Roll of copper Connection screws
Rated current max.	500 A
Rated operating voltage	690 V, 4~
Cable outlet	Bottom
For bar systems with center-to-center spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications.
Number of poles	4-pole
Dimensions	Width: 185 mm Height: 300 mm Width: 7.28 " Height: 11.8 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
To fit manufacturer (model)	Siemens
To fit manufacturer (model)	Siemens (VL400)
Packaging unit	1 pc(s).
Net weight	3.36 kg
Gross weight	3.489 kg
Copper weight (kg per piece)	2.103

Features

Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Circuit-breaker component adaptor, 500 A, 690 V, 4-pole, cable outlet bottom, for switchgear make:, Siemens

Approvals

Explanations	Declaration of conformity
--------------	---------------------------