

**Rittal – The System.**

Faster – better – everywhere.



**SV 9346.000**

# NH In-line Fuse-Switch Disconnecter

State: 4/29/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9346.000 - NH In-line Fuse-Switch Disconnecter



## Features

Model No.	SV 9346.000
Material	Fiberglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Color	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
Supply includes	3 mounting hooks
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	160 A
Rated operating voltage	690 V, 3~
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 50 mm Height: 400 mm Width: 1.97 " Height: 15.7 "

# Features

Connection of round conductors	2.5 - 95 mm <sup>2</sup>
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Number of poles	3-pole
Round conductor cross-section	2.5 - 95 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	1.1 kg
Gross weight	1.3 kg
Copper weight (kg per piece)	0.75
Customs tariff number	85369095
ETIM 9	EC001046
ECLASS 8.0	27371402
Product description	SV NH slimline fuse-switch disconnecter, size 00, 160 A, 690 V, 3-pole, box terminal, 60 mm

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK