

Rittal – The System.

Faster – better – everywhere.



SV 9346.030 NH In-line Fuse-Switch Disconnecter

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9346.030 - NH In-line Fuse-Switch Disconnecter



Features

| | |
|---|---|
| Model No. | SV 9346.030 |
| Material | Fiberglass-reinforced polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper |
| Color | Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016 |
| Supply includes | 3 mounting hooks |
| For bar systems with center-to-center spacing | 100 mm |
| Cable outlet | Top/bottom |
| Type of connection (electrical) | Screw M8 |
| Rated operating current max. | 160 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 00 |
| Test specification | IEC 60 947-3 IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 50 mm Height: 400 mm Width: 1.97 " Height: 15.7 " |

Features

| | |
|--------------------------------|--|
| Connection of round conductors | 2.5 - 95 mm ² |
| Suitable for busbars | Height: 5, 10 mm Height: 0.2, 0.39 " |
| Number of poles | 3-pole |
| Round conductor cross-section | 2.5 - 95 mm ² |
| Packaging unit | 1 pc(s). |
| Net weight | 1.18 kg |
| Gross weight | 1.259 kg |
| Copper weight (kg per piece) | 0.65 |
| Customs tariff number | 85365080 |
| ETIM 9 | EC001046 |
| ECLASS 8.0 | 27371402 |
| Product description | SV NH slimline fuse-switch disconnecter, size 00, 160 A, 690 V, 3-pole, screw M8, 100 mm |

Approvals

| | |
|--------------|---|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity Declaration of conformity UK |