

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.000 RiLineX baying set

State: 4/18/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the complete board, can be used for 550 A and 800 A. Consists of rail connector and contact hazard protection cover. For simple, drill-free baying of boards between two bayed VX enclosures.



## Features

Model No.	RX 9360.000
Benefits	Time saving through complete digital product data Shorter mounting time thanks to pre-mounted complete board Tested short circuit resistance up to max. 65 kA Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC Tested and certified according to IEC and UL Simple expansion and field alignment
Material	Upper part: carbon steel, zinc-plated Contact plate: E-Cu, tin-plated Front cover: polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 35745
Supply includes	3 rail connectors 1 front cover 1 insulating plate
Protection category IP to IEC 60529	IP 2XB

# Features

Standards	IEC 61 439-1/-2 UL 508
Rated current max.	780 A
Rated current (UL)	780 A
Electrical UL ratings (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Rated impulse withstand voltage UImp	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage Ui	1,000 V AC 1,500 V DC
Rated impulse withstand current	103 kA 115.5 kA
Rated short-time withstand current/t	45 kA/200 ms 52.5 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Suitable for Model No.	9360004 9360008 9360024 9360028 9360064 9360068 9360084 9360088
Fundamental frequency	50...60 Hz

# Features

Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	30 x 5/10
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Dimensions	Width: 154 mm Height: 240 mm Depth: 77 mm Width: 6.06 " Height: 9.45 " Depth: 3.03 "
Packaging unit	1 pc(s).
Net weight	1.88 kg
Gross weight	1.924 kg
Copper weight (kg per piece)	0.297
Customs tariff number	85369010
ETIM 9	EC002270
Product description	RX buying set incl. connector for RiLineX Board 3-pole

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration