Rittal – The System.

Faster – better – everywhere.



SV 9340.700
OM adapter

State: 11/5/2026 (Source: www.rittal.com/us-en)

SV 9340.700 - OM adapter with Connection Cables

Features

Model No.	SV 9340.700
Version	With connection cable
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Connection cables (AWG)	AWG 6
Rated current max.	65 A
Rated operating voltage	690 V, 3~
Note	The technical data may vary for UL applications.
Electrical UL ratings (SCCR)	30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7
For bar systems with center-to-center spacing	60 mm
Length of connection cable	130 mm 5.12 ″
Support rail type	Without support frame, 1 x 7.5 x 35 mm
Number of poles	3-pole
Dimensions	Width: 75 mm Height: 208 mm Width: 2.95 ″ Height: 8.19 ″
Support rails Qty/height	1 / 7.5 mm 0.3 ″

© Rittal 2026

Features

Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 ″
Approvals	UL
Packaging unit	1 pc(s).
Net weight	0.259 kg
Gross weight	0.42 kg
Copper weight (kg per piece)	0.116
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 65 A, 690 V, 3-pole, connection cable AWG 6, WH: 75x208 mm, 2 insert strips, metal support rail

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK