

Rittal – The System.

Faster – better – everywhere.



RX 9360.220

RiLineX connection adapter

State: 6/15/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.220 - RiLineX connection adapter

RiLineX connection adapter for 60 mm busbar systems. The adapter boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adapters are screw-fastened onto the board together. The distinguishing features of the connection adapter include a high current-carrying capacity and high short-circuit resistance, plus universal contact hazard protection which adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.



Features

Model No.	RX 9360.220
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current (reference value, IEC)	278 A
Rated current of round conductor max.(IEC)	450 A
Rated current of round conductor max. (UL)	400 A

Features

Rated current of laminated copper bar max. (IEC)	450 A
Rated current of laminated copper bar max. (UL)	400 A
Note	<p>The specified rated current, given as a reference value, is based on the recommended maximum operating current for single-core cable with a permissible conductor temperature of 70 °C in accordance with IEC 61439-1, Table H.1, installation spaced horizontally in free air at an ambient temperature of 55 °C.</p> <p>The specified rated current max. (IEC) describes the recommended maximum operating current of the terminal connection with a temperature rise limit of 70 K in accordance with IEC 61439-1 (Table 6) for conductors spaced free in air. The permissible insulation temperature must be observed.</p>
Electrical UL ratings (SCCR)	<p>27.5 kA - 600 V, RMS, unprotected</p> <p>100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7</p> <p>100 kA - 600 V, 600 A, Class J, JDDZ/7</p>
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	3-pole
Suitable for busbar system	<p>RiLineX</p> <p>RiLine60</p>
Dimensions	<p>Width: 90.5 mm</p> <p>Height: 239.4 mm</p> <p>Depth: 94.6 mm</p> <p>Width: 3.56 "</p> <p>Height: 9.43 "</p> <p>Depth: 3.72 "</p>
Connection of round conductors	10 - 150 mm ²
Clamping area for laminated copper bars for 5 mm bar thickness, (W x H)	<p>20 mm</p> <p>0.79 "</p>

Features

Clamping area for laminated copper bars for 10 mm bar thickness, (W x H)	20 mm 0.79 "
Suitable for busbars	12 x 5/10 15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage U _{Imp}	12 kV
Rated insulation voltage U _i	1,000 V
Power loss max.	19 W 65 BTU/h
Protection category IP to IEC 60529	IP 2X
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %
Fire load	9.69 MJ/m ²
Packaging unit	1 pc(s).
Net weight	0.7 kg
Gross weight	0.815 kg

Features

PCF/VE (cradle-to-gate)	3.87
Customs tariff number	85369010
ETIM 9	EC001531
Product description	<p>RiLineX connection adapter for 60 mm busbar systems. The adapter boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adapters are screw-fastened onto the board together. The distinguishing features of the connection adapter include a high current-carrying capacity and high short-circuit resistance, plus universal contact hazard protection which adapts to the relevant wire gage. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.</p>

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration