

Rittal – The System.

Faster – better – everywhere.



SV 9340.710 OM adapter

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.710 - OM adapter with Connection Cables



Features

| | |
|---|---|
| Model No. | SV 9340.710 |
| Version | With connection cable |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | Chassis: RAL 7035 |
| Connection cables (AWG) | AWG 8 |
| Rated current max. | 40 A |
| Rated operating voltage | 690 V, 3~ |
| Note | The technical data may vary for UL applications. |
| Electrical UL ratings (SCCR) | 30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7 30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 63 A, NLRV/7 65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 |
| For bar systems with center-to-center spacing | 60 mm |
| Length of connection cable | 130 mm 5.12 " |
| Support rail type | Without support frame, 2 x 7.5 x 35 mm |
| Number of poles | 3-pole |

Features

| | |
|------------------------------|---|
| Dimensions | Width: 75 mm Height: 208 mm Width: 2.95 " Height: 8.19 " |
| Support rails Qty/height | 2 / 7.5 mm 0.3 " |
| Suitable for busbars | Height: 5, 10 mm Height: 0.2, 0.39 " |
| Approvals | UL |
| Packaging unit | 1 pc(s). |
| Net weight | 0.379 kg |
| Gross weight | 0.396 kg |
| Copper weight (kg per piece) | 0.088 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV OM adaptor, 40 A, 690 V, 3-pole, connection cable AWG 8, WH: 75x208 mm, 2 insert strips, 2 metal support rails |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |