

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.710 OM adapter

State: 4/16/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.710 - OM adapter with Connection Cables



## Features

|   |   |
|---|---|
| Model No.                                     | SV 9340.710   |
| Version                                       | With connection cable   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Color   | Chassis: RAL 7035   |
| Connection cables (AWG)                       | AWG 8   |
| Rated current max.                            | 40 A  |
| Rated operating voltage                       | 690 V, 3~   |
| Electrical UL ratings (SCCR)                  | 30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7<br>30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7<br>65 kA - 600 V, fuse class J max. 60 A, JDDZ/7<br>65 kA - 480 V, manual motor controller max. 63 A, NLRV/7<br>65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 |
| For bar systems with center-to-center spacing | 60 mm   |
| Length of connection cable                    | 130 mm<br>5.12 "  |
| Support rail type                             | Without support frame, 2 x 7.5 x 35 mm  |
| Note  | The technical data may vary for UL applications.  |
| Number of poles                               | 3-pole  |

# Features

---

|                              |   |
|------------------------------|---|
| Dimensions                   | Width: 75 mm<br>Height: 208 mm<br>Width: 2.95 "<br>Height: 8.19 "   |
| Support rails Qty/height     | 2 / 7.5 mm<br>0.3 "   |
| Suitable for busbars         | Height: 5, 10 mm<br>Height: 0.2, 0.39 "   |
| Approvals                    | UL  |
| Packaging unit               | 1 pc(s).  |
| Net weight                   | 0.379 kg  |
| Gross weight                 | 0.396 kg  |
| Copper weight (kg per piece) | 0.088   |
| Customs tariff number        | 85369095  |
| ETIM 9                       | EC001531  |
| ECLASS 8.0                   | 27370304  |
| Product description          | SV OM adaptor, 40 A, 690 V, 3-pole, connection cable AWG 8, WH: 75x208 mm, 2 insert strips, 2 metal support rails |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | ABS<br>DNV-GL<br>Lloyds Register of Shipping<br>UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK          |