

Rittal – The System.

Faster – better – everywhere.



RX 9360.612

RiLineX CB device adapter

State: 1/22/2026 (Source: ittal.com/us-en)



FRIEDHELM LOH GROUP

RX 9360.612 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "universal" version with sliding nuts offers maximum flexibility for switch installation. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

Model No.	RX 9360.612
Version	universal
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 connection compartment covers
Protection category IP to IEC 60529	IP 2XB
Rated impulse withstand voltage UImp	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V

Features

Overvoltage category	4
Contamination level	3
Clamping area for laminated copper bars (W x H)	15 x 6 mm 0.59 x 0.24 "
Number of poles	3-pole
Cable outlet	Bottom
Type of connection (electrical)	Screw M8
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C -13 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Dimensions	Width: 108.7 mm Height: 251.4 mm Depth: 62.8 mm Width: 4.28 " Height: 9.9 " Depth: 2.47 "
Packaging unit	1 pc(s).
Net weight	1.472
Gross weight	1.474
Copper weight (kg per piece)	0.608

Features

Customs tariff number 85369095

EAN 4028177997080

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity