

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.612

## RiLineX CB device adapter

State: 6/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.612 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "universal" version with sliding nuts offers maximum flexibility for switch installation. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. Version for cable outlet at the bottom.



## Features

|  |  |
|--|--|
| Model No.  | RX 9360.612  |
| Version  | universal  |
| Benefits   | Direct mounting of compact circuit breaker MCCB on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Quick and easy pre-assembly of standard switch types outside the control cabinet |
| Material   | Polyamide (PA 6)<br>Fire behavior corresponding to UL 94   |
| Color  | RAL 9005<br>RAL 35745  |
| Supply includes                                  | Incl. 3 connection compartment covers  |
| Protection category IP to IEC 60529              | IP 2XB   |
| Rated impulse withstand voltage U <sub>Imp</sub> | 8 kV   |

# Features

|                                   |  |
|-----------------------------------|--|
| Rated voltage                     | 690 V AC<br>600 V AC (UL)  |
| Rated insulation voltage Ui       | 1,000 V  |
| Contamination level               | 3  |
| Number of poles                   | 3-pole   |
| Cable outlet                      | Bottom   |
| Cross-section                     | 15 mm <sup>2</sup><br>6 mm <sup>2</sup>  |
| To fit manufacturer (model)       | Easily find the right device adapter with our selection guide in the Downloads area.                   |
| Suitable for busbar system        | RiLineX<br>RiLine60  |
| Fundamental frequency             | 50...60 Hz   |
| Ambient humidity (non-condensing) | 10...90 %  |
| Suitable for busbars              | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| Operating temperature range       | -25 °C...55 °C<br>-13 °F...131 °F  |
| Storage temperature range         | -25 °C...75 °C<br>-13 °F...167 °F  |
| Dimensions                        | Width: 109 mm<br>Height: 251.4 mm<br>Depth: 62.8 mm<br>Width: 4.29 "<br>Height: 9.9 "<br>Depth: 2.47 " |
| Fire load                         | 8.086 MJ/m <sup>2</sup>  |
| Packaging unit                    | 1 pc(s).   |
| Net weight                        | 1.472 kg   |
| Gross weight                      | 1.474 kg   |

# Features

---

|                              |   |
|------------------------------|---|
| Copper weight (kg per piece) | 0.608   |
| PCF/VE (cradle-to-gate)      | 9.96  |
| Customs tariff number        | 85369095  |
| ETIM 9                       | EC001531  |
| Product description          | RX CB device adapter 250 A, 3-pole, version: Universal Fix, cable outlet at bottom, W: 105 mm |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | UL + C-UL (listed)                           |
| Explanations | Declaration of conformity<br>PCF-declaration |