Rittal – The System.

Faster – better – everywhere.



RX 9360.720


RiLineX device adapter


State: 11/5/2026 (Source: www.rittal.com/us-en)

RX 9360.720 - RiLineX device adapter

Component adapter 45 mm. Snap-on mounting of components.







Features

Model No.	RX 9360.720
Version	With connection cable
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 12
Rated current (max.)	25 A
Rated current of round conductor	25 A
Rated current round conductor (UL)	25 A

© Rittal 2026

Features

Electrical UL ratings (SCCR)	5 kA - 600 V, RMS, unprotected 100 kA - 600 V, fuse class RK5 max. 30 A, JDDZ/7 50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7 65 kA - 480 V, Combination Motor Controller max. 16 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 12.5 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 40 A, NKJH/7
Cable outlet	Bottom
For bar systems with center-to-center spacing	60 mm
Length of connection cable	160 mm 6.3 ″
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm Width: 1.77 ″ Height: 9.43 ″ Depth: 1.43 ″
Support rails Qty/height	1 / 10 mm 0.39 ″
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Rated impulse withstand voltage UImp	8 kV
Rated insulation voltage Ui	1,000 V

Features

Protection category IP to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %
Fire load	3.419 MJ/m²
Packaging unit	4 pc(s).
Net weight	1.36 kg
Gross weight	1.39 kg
Copper weight (kg per piece)	0.096
PCF/VE (cradle-to-gate)	8.78
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX component adapter 25 A, AWG 12, 3-pole, W: 45 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration