
Rittal – The System.

Faster – better – everywhere.





RX 9360.798

RiLineX device adapter

State: 11/14/2026 (Source: www.rittal.com/us-en)

RX 9360.798 - RiLineX device adapter

RiLineX device adapter (80 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar systems. With integral threaded inserts. The threaded inserts provided are suitable for mounting the following switchgear: ABB MS495/496/497, Schneider Electric GV3 and Siemens Sirius S3. Other devices may also be used, provided support rails 9320120 are used with this device adapter.

Features

Model No.	RX 9360.798
Version	With connection cable
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 4
Rated current (max.)	80 A

© Rittal 2026

Features

Rated current of round conductor	80 A
Rated current round conductor (UL)	80 A
Electrical UL ratings (SCCR)	100 kA - 600 V, fuse class J max. 200 A, JDDZ/7 65 kA - 480 V, circuit breaker max. 70 A, DIVQ/7 50 kA - 480 V, Combination Motor Controller max. 100 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 75 A, NKJH/7
Cable outlet	Bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 72 mm Height: 239.4 mm Depth: 36.6 mm Width: 2.83 ″ Height: 9.43 ″ Depth: 1.44 ″
To fit manufacturer (model)	ABB (MS 495, MS 496, MS 497) Siemens (S3)
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Rated impulse withstand voltage UImp	8 kV
Rated insulation voltage Ui	1,000 V

Features

Protection category IP to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %
Fire load	4.748 MJ/m²
Packaging unit	1 pc(s).
Net weight	0.7 kg
Gross weight	0.702 kg
Copper weight (kg per piece)	0.246
PCF/VE (cradle-to-gate)	3.9
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX component adapter 80 A, AWG 4, 3-pole, W: 72 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration