Rittal – The System.

Faster – better – everywhere.





SV 9341.050 PLS Busbar Supports

State: 12/14/2025 (Source: rittal.com/us-en)



SV 9341.050 - PLS Busbar Supports

For PLS special busbars 800 A/1600 A, 3-pole and 4-pole, suitable for top-mounting.

Features

Model No.	SV 9341.050
Material	Polyamide
	Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
	1500 V (DC)
Electrical UL ratings (SCCR)	14 kA - 600 V, support spacing 500 mm, busbars PLS 800
	22 kA - 600 V, support spacing 200 mm, busbars PLS 800
	50 kA - 600 V, support spacing 250 mm, PLS 800 busbars, circuit breaker max. 600 A, DIVQ/7
	50 kA - 600 V, support spacing 250 mm, busbars PLS 800, fuse
	class L max. 800 A, JDDZ/7
	65 kA - 480 V, support spacing 150 mm, busbars PLS 800, circuit
	breaker max. 600A, DIVQ/7
	65 kA - 600 V, support spacing 150 mm, busbars PLS 800, fuse
	class max. 600 A, JDDZ/7
Note on Model No.:	The use of a base tray is required for UL applications.
	UL approval only applies in conjunction with AC application
Top-mounting	Yes
Number of poles	3-pole
Suitable for busbars	PLS 800
Suitable for Model No.	3516.000
	3527.000
	3528.000
	3528.010
	3529.000
With internal attachment	Yes

© Rittal 2025

Features

Center-to-center spacing of busbars	60 mm
Approvals	UL
Packaging unit	4 pc(s).
Net weight	0.32
Gross weight	0.362
Customs tariff number	85469010
EAN	4028177525634
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals	ABS Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3