

Rittal – The System.

Faster – better – everywhere.



RX 9360.825

RiLineX fuse switch disconnecter

State: 4/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.825 - RiLineX fuse switch disconnecter D-switch

RiLineX fuse switch disconnecter for 60 mm busbar systems. For use with D 01 (via fitting ring) and D 02 fuses (max. 63 A). Also suitable for use with 10 x 38 mm cylinder locks using the retaining springs supplied. Integrated optical LED fuse monitoring. The switch can be locked in the on and off position. Tension clamp terminals up to 16 mm² at an angle of 45° make it easier to connect conductors. The device is suitable for tool-free snap-on installation with semi-automatic rail adjustment for 5 and 10 mm.



Features

| | |
|---------------------------------|--|
| Model No. | RX 9360.825 |
| Benefits | Safe contacting of the fuse links (without screw caps) Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact protection without additional accessories such as screw caps |
| Material | Polyamide (PA 6) Fire behavior corresponding to UL 94 |
| General color | RAL 35745 RAL 9005 |
| Supply includes | 4 fuse switch disconnectors 12 reducers for D 01 fuses |
| Type of connection (electrical) | Spring terminal |

Features

| | |
|--------------------------------------|--|
| Rated current max. | 63 A |
| Rated operating voltage | 400 V AC |
| Cable outlet | Bottom |
| Number of poles | 3-pole |
| Suitable for busbar system | RiLineX RiLine60 |
| Dimensions | Width: 26.8 mm Height: 263 mm Depth: 104.2 mm Width: 1.06 " Height: 10.4 " Depth: 4.1 " |
| Connection of round conductors | 16 mm ² |
| Suitable for busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Standards | IEC 60 947-3 |
| Rated insulation voltage Ui | 800 V |
| Power loss max. | 5.5 W 19 BTU/h |
| Protection category IP to IEC 60 529 | IP 2XB |
| Maximum operating air humidity | 90 % |
| Operating temperature range | -5 °C...55 °C 23 °F...131 °F |
| Storage temperature range | -25 °C...75 °C -13 °F...167 °F |
| Ambient humidity (non-condensing) | 10...90 % |

Features

| | |
|------------------------------|---|
| Utilization category | AC-22B (400 V/100 A) |
| Fuse inserts | D 02-E 18 |
| Packaging unit | 4 pc(s). |
| Net weight | 1.784 kg |
| Gross weight | 1.792 kg |
| Copper weight (kg per piece) | 0.105 |
| Customs tariff number | 85365080 |
| ETIM 9 | EC001040 |
| Product description | RX fuse switch disconnecter 63 A, 3-pole, with LED, W: 27 mm (D-switch) |

Approvals

| | |
|--------------|--|
| Explanations | Declaration of conformity PCF-declaration |
|--------------|--|