Rittal – The System.

Faster – better – everywhere.



RX 9360.825

RiLineX fuse switch disconnector

State: 11/6/2026 (Source: www.rittal.com/us-en)

RX 9360.825 - RiLineX fuse switch disconnector D-switch

RiLineX fuse switch disconnector for 60 mm busbar systems. For use with D 01 (via fitting ring) and D 02 fuses (max. 63 A). Also suitable for use with 10 x 38 mm cylinder locks using the retaining springs supplied. Integrated optical LED fuse monitoring. The switch can be locked in the on and off position. Tension clamp terminals up to 16 mm² at an angle of 45° make it easier to connect conductors. The device is suitable for tool-free snap-on installation with semi-automatic rail adjustment for 5 and 10 mm.







Features

Model No.	RX 9360.825
Benefits	Safe contacting of the fuse links (without screw caps) Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm² Complete contact protection without additional accessories such as screw caps
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
General color	RAL 35745 RAL 9005
Supply includes	4 fuse switch disconnectors 12 reducers for D 01 fuses
Type of connection (electrical)	Spring terminal

© Rittal 2026

Features

Rated current max.	63 A
Rated operating voltage	400 V AC
Cable outlet	Bottom
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 263 mm Depth: 104.2 mm Width: 1.06 ″ Height: 10.4 ″ Depth: 4.1 ″
Connection of round conductors	16 mm²
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Overvoltage category	4
Contamination level	3
Standards	IEC 60 947-3
Rated insulation voltage Ui	800 V
Power loss max.	5.5 W 19 BTU/h
Protection category IP to IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %

© Rittal 2026

Features

Utilization category	AC-22B (400 V/100 A)
Fuse inserts	D 01 (with reducer) D 02 10 x 38 mm
Fire load	5.437 MJ/m²
Packaging unit	4 pc(s).
Net weight	1.784 kg
Gross weight	1.792 kg
Copper weight (kg per piece)	0.105
PCF/VE (cradle-to-gate)	11.81
Customs tariff number	85365080
ETIM 9	EC001040
Product description	RX fuse switch disconnector 63 A, 3-pole, with LED, W: 27 mm (D-switch)

Approvals

Explanations	Declaration of conformity PCF-declaration