

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adapter

State: 7/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX connection adapter

RiLineX connection adapter for 60 mm busbar systems. The connection adapter is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adapter boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adapter is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.



Features

Model No.	RX 9361.300
Benefits	Mounting on the busbar system and cable connection with just one screw
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current (guideline value, IEC)	1,318 A
Max. rated current of laminated copper bar (IEC)	1,500 A
Max. rated current of laminated copper bar (UL)	1,380 A

Features

Note	<p>The specified rated current as a guideline value is based on the recommended maximum operating current for single-wire cables with an admissible conductor temperature of 70 °C to IEC 61439-1, Table H.1 when laid horizontally in free air, at an ambient temperature of 55 °C.</p> <p>The specified max. rated current (IEC) describes the recommended max. operating current of the terminal connection with a temperature rise limit of 70K to IEC 61439-1 (Table 6) for conductors laid in free air with clearance. Please note the maximum admissible insulation temperature.</p>
Electrical UL ratings (SCCR)	<p>52.5 kA - 600 V, RMS, unprotected</p> <p>100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7</p> <p>100 kA - 600 V, fuse class L max. 2000 A, JDDZ/7</p>
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	1-pole
Suitable for busbar system	<p>RiLineX</p> <p>RiLine60</p>
Dimensions	<p>Width: 72.3 mm</p> <p>Height: 119.4 mm</p> <p>Depth: 117.4 mm</p> <p>Width: 2.85 "</p> <p>Height: 4.7 "</p> <p>Depth: 4.62 "</p>
Clamping area for laminated copper bars (W x H)	<p>50 x 20 mm</p> <p>1.97 x 0.79 "</p>
Suitable for busbars	<p>15 x 10</p> <p>20 x 10</p> <p>30 x 10</p>
Rated voltage	<p>1,000 V AC</p> <p>1,500 V DC</p> <p>600 V AC (UL)</p> <p>600 V DC (UL)</p>
Contamination level	3

Features

Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage U _{Imp}	12 kV
Rated insulation voltage U _i	1,000 V
Protection category IP to IEC 60 529	IP 2X
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non- condensing)	10...90 %
Number of connections	2
Fire load	5.704 MJ/m ²
Packaging unit	1 pc(s).
Net weight	0.65 kg
Gross weight	0.688 kg
PCF/VE (cradle-to-gate)	2.69
Customs tariff number	85369010
ETIM 9	EC001531
Product description	RiLineX connection adapter for 60 mm busbar systems. The connection adapter is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adapter boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adapter is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration
