Rittal – The System.

Faster – better – everywhere.



SV 9342.200

Connection Adapters

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9342.200 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

Features

Model No.	SV 9342.200
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	63 A
Rated operating voltage	690 V, 3~
Note	The technical data may vary for UL applications. UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar support 9340.050/9341.050/9342.050.
Electrical UL ratings (SCCR)	65 kA - 600 V, fuse class J max. 60 A, JDDZ/7 65 kA - 480 V, manual motor controller max. 65 A, NLRV/7
Cable outlet	Top
For bar systems with center-to-center spacing	60 mm
Number of poles	3-pole
Dimensions	Width: 20 mm Height: 215 mm Width: 0.79 ″ Height: 8.46 ″
Connection of round conductors	2.5 - 10 mm²
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 ″
Approvals	UL

© Rittal 2026

Features

For busbar thickness	10 mm 0.39 ″
Packaging unit	1 pc(s).
Net weight	0.199 kg
Gross weight	0.206 kg
Copper weight (kg per piece)	0.019
Customs tariff number	85369010
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Connection adaptor, 63 A, 690 V, 3-pole, cable outet top, round conductor connection 2,5-10 mm²

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK