


**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.005**

**RiLineX NH fuse switch  
disconnecter**

State: 7/6/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.005 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in size 00 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with M8 screw connection. Cable outlet can be individually converted at the top or bottom. Including electronic fuse monitoring.



## Features

|                 |   |
|-----------------|---|
| Model No.       | RX 9362.005   |
| Version         | With electronic fuse monitoring<br>For 60 mm busbar systems<br>With electronic fuse monitoring  |
| Benefits        | Cover, lockable and sealable<br>Voltage test through separate opening<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Tool-free conversion of the cable outlet<br>Park position for simplified maintenance work<br>All variants also with electronic fuse monitoring |
| Material        | Polyamide (PA 6)<br>Fire behavior corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated  |
| Color           | RAL 9005<br>RAL 35745   |
| Supply includes | Incl. connection plug for electrical fuse monitoring  |

# Features

|   |  |
|---|--|
| For bar systems with center-to-center spacing | 60 mm  |
| Cable outlet                                  | Top/bottom   |
| Type of connection (electrical)               | Screw M8   |
| Fuse inserts                                  | NH 00<br>NH 000  |
| Rated operating voltage                       | 690 V AC   |
| For NH size                                   | 00   |
| Test specification                            | IEC 60 947-3<br>IEC 60 269-2 (fuse inserts)  |
| Dimensions                                    | Width: 106 mm<br>Height: 229.5 mm<br>Depth: 104.5 mm<br>Width: 4.17 "<br>Height: 9.04 "<br>Depth: 4.11 " |
| Operating temperature range                   | -5 °C...35 °C<br>23 °F...95 °F   |
| Storage temperature range                     | -25 °C...70 °C<br>-13 °F...158 °F  |
| Suitable for busbars                          | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| Suitable for busbar system                    | RiLineX<br>RiLine60  |
| Number of poles                               | 3-pole   |
| Utilization category                          | AC-23B (400 V/100 A)<br>AC-22B (500 V/100 A)<br>AC-21B (690 V/100 A)<br>DC-22B (250 V/100 A)             |
| Contamination level                           | 3  |
| With electronic fuse monitoring               | Yes  |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Protection category IP to IEC 60529 | IP 2XB   |
| Fire load                           | 16.6 MJ/m <sup>2</sup>   |
| Power loss max.                     | 19 W<br>65 BTU/h   |
| Heat loss per fuse insert (max.)    | 12 W   |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 1.135 kg   |
| Gross weight                        | 1.155 kg   |
| Copper weight (kg per piece)        | 0.363  |
| PCF/VE (cradle-to-gate)             | 7.71   |
| Customs tariff number               | 85369095   |
| ETIM 9                              | EC001040   |
| Product description                 | RX NH fuse-switch-connector size 00, 160 A, 3-pole, M8 screw, with fuse monitoring 800 V |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | CQC-CCC                                      |
| Explanations | Declaration of conformity<br>PCF-declaration |