

# Rittal – The System.

Faster – better – everywhere.



## SV 9342.220 Connection Adapters

State: 12/17/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.220 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

## Features

Model No.	SV 9342.220
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	125 A
Rated operating voltage	690 V, 3~
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Note	The technical data may vary for UL applications. UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar support 9340.050/9341.050/9342.050.
Number of poles	3-pole
Dimensions	Width: 55 mm Height: 210 mm Width: 2.17 " Height: 8.27 "
Connection of round conductors, fine wire with wire end ferrule	10 - 25 mm <sup>2</sup>
Connection of round conductors, multi-wire	16 - 35 mm <sup>2</sup>
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "

# Features

Clamping area for laminated copper bars (W x H)	10 x 7.8 mm 0.39 x 0.31 "
Packaging unit	1 pc(s).
Net weight	0.417
Gross weight	0.42
Copper weight (kg per piece)	0.052
Customs tariff number	85369010
EAN	4028177503618
ETIM 9	EC001531
ECLASS 8.0	27370304

# Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity UK