


# Rittal – The System.

Faster – better – everywhere.



## RX 9362.316

## RiLineX NH fuse switch disconnecter

State: 6/9/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.316 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse switch disconnecters, size 3, for 60 mm busbar systems. The cover can be locked, sealed and has visual fuse monitoring. Safe voltage testing is carried out via integrated measuring points on the cover. The NH fuse switch disconnecters have a park position to make the maintenance work easier. Connection design with screwed connection, size M10. Cable outlet can be individually configured to be at the top or bottom. Includes electronic fuse monitoring. Suitable for voltage range between 180 and 400 V.



## Features

|   |  |
|---|--|
| Model No.                                     | RX 9362.316  |
| Version                                       | For 60 mm busbar systems   |
| Benefits                                      | Cover, lockable and sealable<br>Voltage test through separate opening<br>Tool-free conversion of the cable outlet<br>Park position for simplified maintenance work |
| Material                                      | Polyamide (PA 6)<br>Fire behavior corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated   |
| Color   | RAL 9005<br>RAL 35745  |
| For bar systems with center-to-center spacing | 60 mm  |
| Cable outlet                                  | Top/bottom   |
| Type of connection (electrical)               | Screw M10  |
| Rated operating voltage                       | 400 V  |
| For NH size                                   | 3  |

# Features

|                                      |  |
|--------------------------------------|--|
| Test specification                   | IEC 60 947-3<br>IEC 60 269-2 (fuse inserts)  |
| Dimensions                           | Width: 250 mm<br>Height: 349 mm<br>Depth: 135 mm<br>Width: 9.84 "<br>Height: 13.7 "<br>Depth: 5.31 " |
| Operating temperature range          | -5 °C...35 °C<br>23 °F...95 °F   |
| Storage temperature range            | -25 °C...70 °C<br>-13 °F...158 °F  |
| Suitable for busbars                 | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| Number of poles                      | 3-pole   |
| Utilization category                 | AC-23B (400 V/100 A)<br>AC-22B (500 V/100 A)<br>AC-21B (690 V/100 A)<br>DC-22B (250 V/100 A)         |
| Contamination level                  | 3  |
| With electronic fuse monitoring      | Yes  |
| Protection category IP to IEC 60 529 | IP 2XB   |
| Fire load                            | 47.58 MJ/m <sup>2</sup>  |
| Power loss max.                      | 101 kW<br>344,626 BTU/h  |
| Packaging unit                       | 1 pc(s).   |
| Net weight                           | 4.5 kg   |
| Gross weight                         | 4.819 kg   |
| Customs tariff number                | 85369095   |

# Features

---

## Product description

RiLineX NH fuse switch disconnectors, size 3, for 60 mm busbar systems. The cover can be locked, sealed and has visual fuse monitoring. Safe voltage testing is carried out via integrated measuring points on the cover. The NH fuse switch disconnectors have a park position to make the maintenance work easier. Connection design with screwed connection, size M10. Cable outlet can be individually configured to be at the top or bottom. Includes electronic fuse monitoring. Suitable for voltage range between 180 and 400 V.

# Approvals

---

## Explanations

## Declaration of conformity