

# Rittal – The System.

Faster – better – everywhere.



## RX 9363.310 RiLineX NH fuse switch disconnecter

State: 7/3/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9363.310 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in sizes 3 for mounting plates. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with M10 screw connection.



## Features

Model No.	RX 9363.310
Version	With electronic fuse monitoring For mounting panel assembly.
Benefits	Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
for mounting plate assembly	Yes
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10

# Features

Fuse inserts	NH 3
Rated insulation voltage $U_i$	1,000 V
Rated operating voltage	690 V AC
For NH size	3
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298.5 mm Depth: 128.7 mm Width: 9.84 " Height: 11.8 " Depth: 5.07 "
Operating temperature range	-5 °C...35 °C 23 °F...95 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Number of poles	3-pole
Contamination level	3
Protection category IP to IEC 60 529	IP 2XB
Fire load	44.94 MJ/m <sup>2</sup>
Power loss max.	84 W 287 BTU/h
Packaging unit	1 pc(s).
Net weight	3.8 kg
Gross weight	3.882 kg
Copper weight (kg per piece)	1.68
PCF/VE (cradle-to-gate)	25.87
Customs tariff number	85369095
ETIM 9	EC001040

# Features

---

Product description	RX NH fuse-switch-disconnector size 3, 630 A, 3-pole, M10 screw, mounting plate assembly
---------------------	--

# Approvals

---

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration